


**Botron** High Quality Snap-Off Tab grounders are made from the best products on the market. Our heel grounders have the largest cup design with better floor contact and better testing when soiled. With its dual layer construction non-marking interior and conductive outer surface is designed for long wear. The 18" conductive ribbon (snap-off tab) provides a safe static discharge to ground when tucked into your shoe. We sew our own products so we can make it any way you need. The **B7535** has stretch Velcro fastening system for comfort with a built in 1-megohm resistor, we also offer 2meg and no resistor products. **Disclaimer.** All statements of technical information are believed to be true and are based upon tests we believe to be reliable. The proper use and application for this product must be the responsibility of the user. The statements herein shall have no force or effect.



Stretch Velcro for comfort  
Quick on-off attachment  
and removal



**Installation:**

1. Un-strap hook & loop strap and slip the rubber cup onto heel.
2. Pull the hook & loop tight over arch area.
3. Trim conductive ribbon to desired length and place inside of sock or shoe. (skin contact is best)

PROPERTIES	SPECIFICATIONS
------------	----------------

<b>Sole Interior:</b>	Non-Marking
<b>Sole Exterior:</b>	<10 <sup>5</sup>
<b>Material:</b>	Two layer rubber
<b>Ribbon:</b>	Snap-off 18" conductive
<b>Cup Design:</b>	1.5" x 7.5" (others are smaller)
<b>Charge Decay:</b>	<0.01Sec
<b>Thickness:</b>	0.08-0.13mm
<b>RTG: with 1 meg</b>	<2x10 <sup>6</sup> -1x10 <sup>7</sup>
<b>Meets:</b>	ANSI/ESD S.20.20 & Mil 263
<b>3/4" Stretch Hook &amp; Loop:</b>	Fastening system
<b>Packing:</b>	1 per.bag / bags of 10
<b>Custom Sizes:</b>	<b>We sew our own products</b>

**OTHER PRODUCTS:**  
**B7500** Ergo-One heel grounder  
**B7571** Non-Marking heel grounder  
**B7528** D-Ring heel grounder  
**B7591** Red Hi-Visibility heel grounder  
**B7522** Toe grounder  
 Many other heel & toe grounders

**1/5" VERSES 1" CUP DEISGN**  
 50% Better floor contact.  
 50% Better chance to past test when soiled.  
 50% Better fit, will not slip off.

**RELATED TEST EQUIPMENT:**  
**B82250** Dual Tester with stand  
**B82450** Combo tester with stand  
**B8525** Deluxe Dual tester & stand  
**B85502** Calibration unit for testers  
**B8506** Wall test station

**Lean Stream, LLC**  
 2153 O'Toole Avenue, Suite G  
 San Jose, CA, 95131  
 Phone: **408-894-9400**  
 Fax: 408-954-9989  
 Email: [info@lean-stream.com](mailto:info@lean-stream.com) / [www.lean-stream.com](http://www.lean-stream.com)

**SNAP-OFF TAB HEEL GROUNDER**