


**Botron** High Quality Standard Hook & Loop heel grounders are made from the best products on the market. Our heel grounders have the largest cup design with better floor contact and better testing when soiled. With its dual layer construction non-marking interior and conductive outer surface is designed for long wear. The 18" conductive ribbon provides a safe static discharge to ground when tucked into your shoe. We sew our own products so we can make it any way you need. The **B7503** has standard hook & loop fastening system and we can do it in almost any color, with a built in 1-megohm resistor, we also offer 2meg and no resistor products. **Disclaimer.** All statements of technical information are believed to be true and are based upon tests we believe to be reliable. The proper use and application for this product must be the responsibility of the user. The statements herein shall have no force or effect.



**Installation:**

1. Un-strap hook & loop strap and slip the rubber cup onto heel.
2. Pull the hook & loop tight over arch area.
3. Trim conductive ribbon to desired length and place inside of sock or shoe. (skin contact is best)

**PROPERTIES**

**SPECIFICATIONS**

<b>Sole Interior:</b>	Non-Marking
<b>Sole Exterior:</b>	<10 <sup>5</sup>
<b>Material:</b>	Two layer rubber
<b>Ribbon:</b>	conductive 18"
<b>Cup Design:</b>	1.5" x 7.5" (others are smaller)
<b>Charge Decay:</b>	<0.01Sec
<b>Thickness:</b>	0.08-0.13mm
<b>RTG:with 1meg</b>	<2x10 <sup>6</sup> -1x10 <sup>7</sup>
<b>Meets:</b>	ANSI/ESD S.20.20 & Mil 263
<b>3/4" Hook &amp; Loop:</b>	Fastening system
<b>Packing:</b>	1 per.bag / bags of 10
<b>Custom Sizes:</b>	<b>We sew our own products</b>

**OTHER PRODUCTS:**

- B7528 D-Ring heel grounder**
- B7571 Non-Marking heel grounder**
- B7525 Snap-Loc heel grounder**
- B7591 Red Hi-Visibility heel grounder**
- B7522 Toe grounder**
- Many other heel & toe grounders**

**1/5" VERSES 1" CUP DESIGN**

- 50% Better floor contact.
- 50% Better chance to pass test when soiled.
- 50% Better fit, will not slip off.

**RELATED TEST EQUIPMENT:**

- B82250 Dual Tester with stand**
- B82450 Combo tester with stand**
- B8525 Deluxe Dual tester & stand**
- B85502 Calibration unit for testers**
- B8506 Wall test station**

**Lean Stream, LLC**  
 2153 O'Toole Avenue, Suite G  
 San Jose, CA, 95131  
 Phone: **408-894-9400**  
 Fax: 408-954-9989  
 Email: [info@lean-stream.com](mailto:info@lean-stream.com) / [www.lean-stream.com](http://www.lean-stream.com)

**STANDARD HOOK & LOOP HEEL GROUNDNER**